

FEATURES

- **LED Bulb Type:** Ensures long-lasting performance and energy efficiency
- **Flashing Light Effect:** Provides clear visual alerts to enhance safety
- **Sound Level up to 92 dB:** Delivers a powerful audible warning suitable for noisy environments
- **IP43 Rating:** Offers protection against solid objects over 1mm and water spray
- **Wide Operating Temperature Range:** Functions effectively from -20 °C to 50 °C, suitable for various climates
- **ABS Housing Material:** Durable and resistant to impact, ensuring longevity
- **Screw Mount Type:** Facilitates easy and secure installation
- **CE and EAC Approved:** Complies with international safety and quality standards

RS PRO LED Horn-Beacon Combination, IP43
Grey Housing

RS Stock No: 658-300



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO Horn-Beacon Combination is designed to provide both visual and audible alerts in industrial settings. It features a flashing LED light and a sounder, making it ideal for environments where clear and immediate alerts are essential. The combination of light and sound ensures comprehensive notification, enhancing safety and awareness.

General Specifications

Bulb Type	LED
Housing Colour	Grey
Lens Colour	Red
Light Effect	Flashing
Mount Type	Screw
Number of Tones	1
Product Type	Horn-Beacon Combination
Sounder Type	Sounder Beacon

Electrical Specifications

Current Consumption	0.04 A
Current Type	AC
Maximum Supply Voltage	240 V ac

Mechanical Specifications

Housing Material	ABS
------------------	-----

Protection Category

IP Rating	IP43
-----------	------

Operation Environment Specifications

Maximum Operating Temperature	50 °C
Minimum Operating Temperature	-20 °C

Measurement Specifications

Maximum Sound Level	92 dB
Minimum Sound Level	88 dB

Approvals

Standards/Approvals	CE, EAC
---------------------	---------