

JP.T – 3/8" Phillips Bit Sockets



Description:

- **HIGH PERFORMANCE** - Designed and manufactured for extremely high tightening forces
- **BIT PROFILE** - For Female drive Fasteners
- **NECK-DOWN DESIGN** - Facilitating the use in narrow spaces
- **Matte finish**
- **ISO 2725-1 - DIN3124 – ISO 1174-1**

	Fastener Head Size	Square Drive	Diameter (mm)	Length (mm)	Weight (g)
JP.1T	PH1	3/8"	17.9	50	31
JP.2T	PH2	3/8"	17.9	50	33
JP.3T	PH3	3/8"	17.9	50	43