Features

- Cooking Controller
- Temperature Sensor Input (TC,RTD)
- 4 Digits Display
- 24Vac/dc Power Supply
- Time Control
- Heating Control Relay (7A@250Vac)
- Time Control Relay (5A@250Vac)
- Steam Control Relay (5A@250Vac)

RS PRO Cooking Controller

RS Stock No:
874115



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Cooking Controller

Product Description

Digital PID and ON/OFF Cooking Control
Temperature Sensor Input Type (TC,RTD)
1X Relay Output (7A@250Vac)
2X Relay Output (5A@250Vac)
4 Digits display
Applications Fields:
- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications

General Specifications

Supply Voltage and Power	24Vac/dc 50/60Hz – 2,5A
Sensor Inputs	Temperature Sensor Input Type (TC,RTD)
Output (Heater Control)	1X Relay Output (7A@250Vac) at resistive Load
Output (Time Control)	1X Relay Output (5A@250Vac) at resistive Load
Output (Steam Control)	1X Relay Output (5A@250Vac) at resistive Load
Accuracy	Scale ± %0.25

Mechanical Specifications

Dimension	96 mm x 96 mm 96 mm
Panel	IP65 at front, IP20 at rear
Max. Operating Temperature / Humidity	50°C / 90 % max. (None condensing)

Electrical Connection

