



**Datasheet** 

Stock No: 283-8324

# RS Pro Stainless Steel, Steel Hydraulic Check Valve, G 3/4



### **Product Details**

#### Steel Non-return Valves

Manufactured from steel these non-return valves are seated metal to metal by means of spring loaded ball housed in an ABS plastic guide.

#### Note

Not suitable for use with water.

Check Valves





## **Specifications**

Manufacturer Series	FT260
Connection Port Thread	G 3/4
Maximum Flow Rate	80L/min
Body Material	Stainless Steel, Steel
Maximum Operating Pressure	350 bar
Thread Standard	G
Thread Size	3/4 in
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C