



R-299

Durable heavy-duty impact protection gloves, offering advanced cut resistance and grip



Impact



Abrasion Protection

Cut

Durable heavy-duty impact protection gloves, offering advanced cut resistance and grip

- **Enhanced grip:** RINGERS® R299 impact gloves feature a durable grip system on the palm and fingers, for high-performance grip levels in heavy-duty conditions
- **Advanced defenses:** These RINGERS® gloves also boast an additional palm layer, granting wearers heightened cut resistance for a variety of applications
- **Specialized protection:** Featuring a patented TPR (thermoplastic rubber) design developed with F3 Technology™, these gloves provide ANSI/ISEA 138-2019 Level 2 impact protection for the knuckles, thumb, and full length of the fingers
- **Enhanced features:** These heavy-duty gloves also feature a convenient extended airprene wrist closure with TPR pull tab, as well as Kevlar® palm stitching and an increased visibility external surface, for added safety and security



Industries

- Oil and gas
- Construction
- Manufacturing
- Mining
- Industrial

Applications

- Engagement and release of drill string slips
- Chaining up pipes
- Installation and dismantling of rigs
- Preparation of site - unloading of lines and valves
- Handling iron - rigging work
- Handling of tools
- Seizing structural and body parts



R-299

Durable heavy-duty impact protection gloves, offering advanced cut resistance and grip

Key Features

- **Durable grip system:** For advanced hand protection with superb grip
- **Additional palm layer:** Heightened cut resistance
- **Patented TPR design:** Knuckles, thumb and finger-length impact protection

Performance Standards & Regulatory Compliance



EN388: 2016



ANSI/ISEA 105-2024



ANSI/ISEA 138-2019



GOLD | Top 5%
ecovadis
Sustainability Rating
AUG 2024

4X44FP

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R299	Liner Material: HPPE Cuff Style: Extended neoprene wrist closure		8, 9, 10, 11, 12, 13	Red	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

