









NO	DESCRIPTION	DATE
①	ADD MIS PART NO. 35.0 → 35.1 ; 40.7 → 40.8	04.01.04'
②	ADD A-A SECTION ø2.7 → ø2.7 <sup>+0.1</sup> <sub>-0</sub>	12.02.04'
③	16.5 → 16.2	07.26.06'
④	ADD (P/N:544-3402)	04.13.10'
⑤	2.5 → 2.6 ; 16.2 → 16.0	06.28.10'



△ A-A SECTION



△ MIS PART NO: 069-0009H-03 (P/N:544-3402) △

APPROVED

by \_\_\_\_\_ DATE: \_\_\_\_\_



7	SPRING	IRON	1	ZINC
6	SCREW	IRON	2	ZINC
5	SCREW	IRON	2	ZINC
4	SCREW	IRON	2	ZINC
3	SCREW	IRON	2	ZINC
2	CAP	ABS	1	NONE
1	BODY	ABS	1	NONE
NO	DESCRIPTION	MATERIAL	Q' TY	FINISH

DESCRIPTION		9PIN D-HOOD-3	
製圖	DRAWN Yoko	TOLERANCE .X ±0.2	品名 9PIN D-HOOD-3
檢圖	CHECK Angela	.XX ±0.1	TITLE ROHS COMPLIANT
認定	APPROVAL Angela	.XXX ±0.05	單位 mm(in)
		ANGLE ±5°	比例 2:1
日期	10.30.96'	版次	A-5
DWG.NO.	55-0085		