

Contact insert - RC-09S1N8A0000 - 1596303

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Contact insert, Number of positions: 8+1, Type of contact: Socket, Crimp connection



The figure shows the 6-pos. product version



Key commercial data

Packing unit	50 pc
Minimum order quantity	10 pc
GTIN	 4 046356 210515
Weight per Piece (excluding packing)	2.92 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

General

Note	Order information Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Crimp connection
Type of contacts	Socket
Number of positions	9
Contact diameter of power contacts	2 mm
Nominal current per power contact at 25°C	20 A
Contact diameter of signal contacts	1 mm
Nominal current per signal contact at 25°C	8 A

Material

Insulator material	PA66
--------------------	------

Specifications according to DIN EN 61984:2001

Contact insert - RC-09S1N8A0000 - 1596303

Technical data

Specifications according to DIN EN 61984:2001

Nominal / operating voltage of power contacts	300 V
Rated surge voltage of power contacts	2.5 kV
Surge voltage category of power contacts	II
Pollution degree of power contacts	3
Nominal / operating voltage of signal contacts	300 V
Surge voltage category of signal contacts	II
Pollution degree of signal contacts	3

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Accessories

Accessories

Crimp contact

Crimp contact - RC-12S2000 - 1599600



Crimp contact, turned, Single contact, Contact diameter: 1 mm, Crimp range: 0.14 mm²...0.56 mm²

Contact insert - RC-09S1N8A0000 - 1596303

Accessories

Crimp contact - RC-5AS2000 - 1603509



Crimp contact, turned, Contact diameter: 2 mm, Crimp range: 1.5 mm²...2.5 mm²


Crimp contact - RC-5CS2000 - 1603517



Crimp contact, turned, Contact diameter: 2 mm, Crimp range: 1 mm²...1.5 mm²

Drawings

Schematic diagram



Schematic diagram

