

Sub-base VABS-K2-10S-16-M5-P

Part number: 8186875

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	10
Nominal size	1.6 mm
Valve size	10 mm
Fluid connection	Female thread M5
Mounting position	optional
Design	Connection direction at side
Max. number of valve positions	1
Flow direction	Non-reversible
Operating medium	Liquid media Gaseous media
Note on operating and pilot medium	Observe resistance of materials that come into contact with the media
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 70 °C
Suitable for use with food	See supplementary material information
Media temperature	0 °C ... 50 °C
Ambient temperature	0 °C ... 50 °C
Max. tightening torque for valve mounting	0.2 Nm
Max. tightening torque for fitting	1 Nm
Max. tightening torque	0.6 Nm
Product weight	20 g
Mounting method for sub-base	With through-hole
Mounting method for valve	Via female thread
Note on materials	RoHS-compliant
Material sub-base	PEEK