

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Customers Also Bought



TE Part #927824-1
SPT REC 6.3 Contact SRC Sn



TE Part #DT06-3S-CE04
PLG, 3P, GRY, E, XCAP



TE Part #1443997-1
BASE ASSEMBLY, 60 POSITION, BB




TE Part #1443996-4
COVER, 60 POS, W/O FUSE HLDR/NO EXT TEXT



TE Part #2098164-1
Cover, 60 Position PDM



TE Part #1416200-9
V23061B1010A301




TE Part #1326133-1
RECEPTACLE HOUSING, 18 POSITIO



TE Part #1379100-1
COV+LEV MQS 18W 0DEG BLK



TE Part #1060-16-0177
PIN, SF, SIZE 16, 14-18, SN/SN



TE Part #1-1393310-8
26A1348A=TERMINAL,CRMP,QC.250,

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_1-1393305-3_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1393305-3_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1393305-3_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Automotive Relay Application Notes

English



Connectors for Mini (Shrouded)/Maxi ISO, Connectors Production Production North America, Accessories

English

Product Specifications

Definitions General Purpose Relays

English