



RS PRO LED BEACONS INSTALLATION GUIDE

222-2464, 222-2465, 222-2466, 222-2467, 222-2468
222-2469, 222-2470, 222-2471

The RS Pro LED Beacons are supplied fully assembled and ready for immediate installation. The unit offers two mounting options, either stud mount or surface mount using the two piece fixing plate supplied. One plate is fixed to the appropriate surface the other to the beacon and the two plates then click together.

This beacon is designed to comply with IP65 when correctly installed. To ensure a weatherproof installation the beacon must be fitted with the Foam gasket and mounted on a flat panel or surface. The panel or surface should be drilled to accept the wires and M4 studs as shown. (see below)

A suitable cable sleeve must be used where necessary to restrict the access to the power cables.

Ensure correct wiring procedures are followed during installation: -

12-24VAC/DC Version

Ensure that the Red wire is connected to the Positive terminal, the Black wire to the Negative terminal a flashing effect and the grey wire connected to the Negative terminal for a continuous effect.

110-240VAC Version

Ensure that the Red wire is connected to the Positive terminal, the Black wire to the Negative terminal for flashing effect and grey wire connected to the Negative terminal for a continuous effect.

