

Description

STAINLESS STEEL TOP PLATE CASTOR, GREY RUBBER 100MM

Fixed

JF3BA100-325L



Part Number

Swivel

JP3BA100-325L




Swivel and brake

JP3BD100-325L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	100 mm		
Overall Height H	134 mm ±1		
Size of plate A X B	76 x 70 mm±1		
Plate hole centres a x b	60 x 50 mm±0,3		
Plate hole	8,3 mm		
Offset F ±1	\	35 mm	35 mm
Width of Tread	27 mm±0,5		
Hardness of tread	shore A ± 93		
Load capacity	80 Kg		
Weight	0,38 kg	0,46 kg	0,51 kg
Temperature	- 5 / + 50 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Fastening by top plate.
Total lock. Plastic pedal.

Wheel :

Wheel centre made of Grey Polypropylene.
Tread : Thermoplastic rubber, grey non marking. Plain bearing.

Features :

Low starting effort,
Bonded Rubber,
Corrosion resistant, easy to clean
Suited for Food industry, Hospital or Industrial Kitchen equipment.