



Main

| | |
|---------------------------|---------------|
| Range of product | Mita |
| Product or component type | Mini trunking |
| Colour tint | White |
| Quantity per set | 90 m |

Complementary

| | |
|--------------------------|---|
| Compartment partitioning | 1 compartment |
| Trunking dimension | 25 x 16 mm |
| Fixing mode | Screw-fixed |
| Material | UPVC (unplasticized polyvinyl chloride) |
| Length | 3000 mm |
| Height | 25 mm |
| Width | 16 mm |

Environment

| | |
|---------------------------------------|------------|
| Standards | BS 4678-4 |
| Ambient air temperature for operation | -5...60 °C |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration |

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations

Contractual warranty

Warranty

18 months
