

# DP-TB-2L - Spacer plate



3059977

<https://www.phoenixcontact.com/gb/products/3059977>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacer plate, compensates for the offset at the lower level when standard terminal blocks are mounted side-by-side, depth: 25 mm, width: 2.5 mm, height: 67.2 mm, color: dark gray



## Commercial data

Item number	3059977
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE1Z1X
Product key	BEKZ1X
GTIN	4046356643900
Weight per piece (including packing)	3.693 g
Weight per piece (excluding packing)	3.59 g
Customs tariff number	85389099
Country of origin	DE

# DP-TB-2L - Spacer plate



3059977

<https://www.phoenixcontact.com/gb/products/3059977>

## Technical data

### Product properties

Product type	End cover
--------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	traffic grey B (RAL 7043)
Material	PA
Flammability rating according to UL 94	V0

### Dimensions

Width	2.5 mm
End cover width	2.5 mm
Height	67.2 mm
Depth	25 mm

# DP-TB-2L - Spacer plate



3059977

<https://www.phoenixcontact.com/gb/products/3059977>

## Classifications

### ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

### ETIM

ETIM 9.0	EC000886
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# DP-TB-2L - Spacer plate



3059977

<https://www.phoenixcontact.com/gb/products/3059977>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)