

## 8000 J 5

Circlip pliers for internal retaining rings

Code	ETIM
6703750	EC002228
EAN	UNSPSC
4010886670378	27-11-21-10
Country of origin	eCl@ss
Austria	21-04-03-01
Customs tariff number	
82032000	



### Article description

- Straight tips
- Black, tips and lock lever zinc-plated
- The toothed bracket stops the pliers legs from straddling beyond the permitted working area
- This ensures safe working even in hidden fitting positions
- Locking pin can be replaced
- Non-crush type release-lever with handle recesses, blue dip-insulated
- Precision machined, oil hardened and annealed
- Pair of replacement tips available

### Article information

Contents (Qty of pieces)	1	Tip diameter	3.5 mm
Net weight [kg]	1,836 kg	Handle design	dip-insulated
Total length [mm]	565 mm	Hardening process	oil-hardened and tempered
Total width [mm]	200 mm	Joint types	applied joint
Total height [mm]	25 mm	Shaft diameter [mm]	122-300
Surface	Black varnished	Shaft diameter [inch]	4.13/16-11.7/8
Design non-sparking	No		