

## R 15-SCHRAUBKAPPE



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 5401
Specification	R 15-SCHRAUBKAPPE
HARTING eCatalogue	<a href="https://harting.com/09150005401">https://harting.com/09150005401</a>

### Identification

Category	Hoods / Housings
Series	R 15
Type of hood/housing	Cover
Description of hood/housing	With fixing cord Thermoplastic

### Version

Locking type	Screw locking
--------------	---------------

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead



**Pushing Performance**  
Since 1945

## Material properties

Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Commercial data

Packaging size	10
Net weight	9.56 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021792
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467