


DP-LPO 35 - Spacer plate

3270545

<https://www.phoenixcontact.com/gb/products/3270545>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Spacer plate, depth: 24.4 mm, width: 16 mm, height: 18.3 mm, color: gray

Commercial data

Item number	3270545
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	BE2Z3X
Product key	BE2Z3X
GTIN	4055626229119
Weight per piece (including packing)	2.74 g
Weight per piece (excluding packing)	2.74 g
Country of origin	PL

DP-LPO 35 - Spacer plate



3270545

<https://www.phoenixcontact.com/gb/products/3270545>

Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

Width	16 mm
Height	18.3 mm
Depth	24.4 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

DP-LPO 35 - Spacer plate

3270545

<https://www.phoenixcontact.com/gb/products/3270545>



Classifications

ECLASS

ECLASS-13.0	27250301
-------------	----------

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

DP-LPO 35 - Spacer plate

3270545

<https://www.phoenixcontact.com/gb/products/3270545>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk