

Datasheet

**Blue 30m Nylon Air Hose, -40 → +80°C,
Application Various**

RS Stock number **386-6257**



Product Details

Superflex Nylon Tube

- Ideally suited to applications requiring a more flexible nylon tube
- High flexibility even at very low temperatures
- Excellent abrasion resistance with a high durability to oil and petrol
- Extremely high impact and chemical resistance
- Silicone free construction
- Maximum working pressure =>12.5 bar
- 30m coils

RS, Professionally Approved Products, gives you professional quality parts across all product categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

Push-in System - Nylon Tube

All coils shown are non anti-static.

Add product to Compare

Specifications

[Find alternatives](#)

To find a similar product, based on selected attributes, click the green button

Application	Air Brake, Fuel & Lube Applications, Industrial & Automotive Production Lines, Instrumentation & Secondary Air Systems
Colour	Blue
Hose Inside Diameter	5.5mm
Hose Outside Diameter	8mm
Length	30m
Manufacturer Series	NMSF
Material	Nylon
Maximum Operating Pressure	13.5 bar
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-40°C