

品種一覧

■定格電圧 630V DC

形名	静電容量(μF)	T寸法(mm)
VC30R2J102K-TS	1,000	1.00+0/-0.25
VC30R2J222K-TS	2,200	1.00+0/-0.25
VC30R2J472K-TS	4,700	1.00+0/-0.25
VC30R2J103K-TS	10,000	1.80+0/-0.40
VC40R2J103K-TS	10,000	1.25+0/-0.30
VC40R2J223K-TS	22,000	1.70+0/-0.40
VC70R2J223K-TS	22,000	1.25+0/-0.30
VC70R2J333K-TS	33,000	1.70+0/-0.40
VC70R2J473K-TS	47,000	1.70+0/-0.40
VC80R2J473K-TS	47,000	1.25+0/-0.30
VC80R2J104K-TS	100,000	2.20+0/-0.50

■定格電圧 250V DC

形名	静電容量(μF)	T寸法(mm)
VC30R2E102K-TS	1,000	1.00+0/-0.25
VC30R2E222K-TS	2,200	1.00+0/-0.25
VC30R2E472K-TS	4,700	1.00+0/-0.25
VC30R2E103K-TS	10,000	1.00+0/-0.25
VC30R2E223K-TS	22,000	1.80+0/-0.40
VC30R2E273K-TS	27,000	1.80+0/-0.40
VC30R2E333K-TS	33,000	1.80+0/-0.40
VC40R2E223K-TS	22,000	1.25+0/-0.30
VC40R2E333K-TS	33,000	1.25+0/-0.30
VC40R2E473K-TS	47,000	1.70+0/-0.40
VC70R2E473K-TS	47,000	1.25+0/-0.30
VC70R2E104K-TS	100,000	1.70+0/-0.40