




Nitrile Disposable Gloves Grip - 7/S - 50 pc

NITRILE DISPOSABLE GLOVES

- Durable and resistant disposable nitrile gloves with a thickness 0.09mm and weight of 8.0gr, reducing the risk of tear and break, increasing productivity.
- Diamond texture pattern to improve grip on metallic tools or in oily and greasy surfaces.
- Chemical resistant ideal to protects from oils, gasoline, thinners, brake fluids, solvents commonly used in automotive garages.
- Excellent dexterity to let users feel the working surface and handle very small parts.
- SMARTSWIPE™ fingertips - allows the use of touch screen devices without removing gloves.
- European Certified for chemical protection: EN ISO 374-1:2016 Type B / KPT, EN ISO 374 -2, EN ISO 374-5 (VIRUS), EN ISO 21420, UKCA, EAC, UKRAINE



Size	Article Number
Pack quantity	7 / S
	50
8 / M	
50	9 / L
	50
10 / XL	
50	11 / XXL
	50