

### Helaguard PCS-90FMC 90° Elbow Compression Fitting, IP65

External thread elbow, nickel plated brass.  
Fulfils IP65.

#### Features and Benefits

- Multipart 90° compression fitting including elastomeric seal



Helaguard PCS-90FMC 90 Elbow Compression Fitting.

Technical Table

Article-No.	Type	Conduit Ø	Thread Size (metric)	Pack Cont.
166-31600	PCS10-90FMC-M16	10	M16	10
166-31601	PCS12-90FMC-M16	12	M16	10
166-31602	PCS16-90FMC-M16	16	M16	10
166-31603	PCS16-90FMC-M20	16	M20	10
166-31604	PCS20-90FMC-M20	20	M20	10
166-31605	PCS25-90FMC-M25	25	M25	10
166-31606	PCS32-90FMC-M32	32	M32	2

All dimensions in mm. Subject to technical changes.

Material Data

Material	Nickel Plated Brass (NPB), Polyamide 6 (PA6)
Colour	Metal (ML)
Operating Temperature	-40 °C to +135 °C



### Helaguard PCS-PCS Compression Coupler, IP65

Nickel plated brass.  
Fulfils IP65.

#### Features and Benefits

- Multipart compression coupler including polyamide seals.
- Joins two conduits



Helaguard PCS-PCS Compression Coupler.

Technical Table

Article-No.	Type	Conduit Ø	Pack Cont.
166-31700	PCS20-PCS20	20	10
166-31701	PCS25-PCS25	25	10

All dimensions in mm. Subject to technical changes.

Material Data

Material	Nickel Plated Brass (NPB), Polyamide 6 (PA6)
Colour	Metal (ML)
Operating Temperature	-40 °C to +135 °C

