

435G adjustable tap wrenches, light alloy body

DIN 1814

	art.	□ mm	L mm
004350108	435G/0	2÷5 M1÷M8	130
004350110	435G/1	2÷6 M1÷M10	190
004350112	435G/1,5	2÷7 M2÷M12	175
004350114	435G/2	3,4÷7 M4÷M12	280
004350121	435G/3	4,9÷12 M5÷M20	380
004350127	435G/4	7÷16 M11÷M27	500
004350132	435G/5	7÷18 M13÷M32	700
004350142	435G/6	11÷24 M18÷M42	800

