



Save as PDF



## Peli lights - Dust proof - LED technology head up



The 2640 is a powerful Halogen/LED combo hands-free light for any task, big or small. Flip the switch up and you've got 3 LEDs: bright and efficient. Perfect for close-up work and tasks that require intense white light. For jobs that demand a powerful beam, flip the switch down for the halogen mode. Cut through thick smoke and dust. The body is tough ABS resin that's corrosion proof and resistant to extreme temperatures. The 90° pivoting head allows you to aim light right where you need it. The light weight battery pack houses 4 AA alkaline cells (included). The HeadsUP Lite 2640 comes with a rubber strap for hard hat use and an adjustable cloth strap for bare head. Certified to ATEX Zone 2 (Category 3).



### Materials

Body	Lens	Shroud	Switch Type
ABS Resin	Polycarbonate Resin	ABS Resin	Hi/Lo side switch
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
	Stainless Steel and Brass Nickel Plate	Ethylene Propylene	

### Configuration

Cat. #	Description
--------	-------------

### Peli lights - Dust proof - LED technology head up Accessories

Cat. #	Description
2644	<a href="#">HeadsUp Lite 2640 Lamp</a>

### Peli lights - Dust proof - LED technology head up

#### ANSI FL1 Specifications

	High	Low
<b>LIGHT SOURCE.</b>	Incandescent (Halogen)	
<b>BATTERIES</b>	4 AA Alkaline (Included)	
<b>CHARGE TIME</b>	N/A	
<b>VOLTAGE</b>	6	
<b>LENGTH</b>	6.7 cm (2.63")	
<b>WEIGHT W/ BATTERIES</b>	0.17 kg (6 oz.)	
<b>WEIGHT W/O BATTERIES</b>	0.21 kg (7.4 oz.)	

**LIGHT OUTPUT**

**RUNTIME (hours/min)**

**BEAM DISTANCE (meters)**

**PEAK BEAM INTENSITY (candela)**

FL1 STANDARD	High	Low
		9.00 LUMENS
	2h 45m	50 hrs.
	46m	20 m.
	586cd	103cd

### Approvals



- II 3 G EEx nL IIC T3X

Certificate: TRL Report# XU1006/4804



- Listed 4567/E184884 Class I, Div. 2;

Gp.A,B,C, D T3.