



Part No. 112090301

Series 209 Standard guns

3D

PDF

[Inquiry List](#)

Class title

Regulator

Tube

Removable tube

Connection

Rc 1/4"

Noise level (db)

87 dB

Flow capacity (l/min)

232 l/min

Max working pressure (bar)

8 bar (116 PSI)

Standards

OSHA STD 01-13-001

Min. burst pressure (bar)

32 bar (928 PSI)

Material

POM (body), TPE (soft grip), brass (tube)

Media

Air and non-explosive water based liquids

Min temperature (C)

-20°C — +60°C (-4°F — +140°F)

209 Standard guns

The 209 Standard gun is a highly versatile and reliable tool for a wide variety of applications. It comes in four distinct options to meet the needs of different users. The combination of a durable design and a lightweight plastic body is crucial in creating a long-lasting, user-friendly and resilient product. The 209 blow gun is an effective tool and perfect solution for handling both air and non-explosive fluids.



Check with an authorized CEJN distributor for availability and prices. All measurements are in mm. Other connections and sealing material on request. Some part numbers may be subject to minimum order quantities. CEJN reserves the right to make changes without further notification. Thread connections are listed according to ISO standards, unless stated otherwise.
