ACS480-04-07A3-4

ACS480-04-07A3-4 Pcont.max:3kW, Icont.max:6,8A

General Information

Global Commercial Alias	ACS480-04-07A3-4
Product ID	3AXD50000047769
ABB Type Designation	ACS480-04-07A3-4
EAN	6438177458975
Catalog Description	ACS480-04-07A3-4 Pcont.max:3kW, Icont.max:6,8A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044084
EAN	6438177458975
Invoice Description	ACS480-04-07A3-4 Pcont.max:3kW, Icont.max:6,8A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	FIPSEEXPU US Drive Services SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU FIDRIEXPU

Dimensions

Product Net Height	223 mm
Product Net Weight	1.77 kg
Product Net Width	73 mm

Additional Information

Product Main Type	ACS480-04-07A3-4
Product Name	Frequency Converter

Categories

Drives → Low voltage AC drives → General purpose drives

Water Utility Solutions → Desalination Plant → Electrical → Drive systems → Drives → Low voltage AC drives → General purpose drives