

FEATURES

- **Polyamide material:** Provides excellent strength and durability for long-lasting performance
- **UV resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **UL 94 V-2 fire behaviour:** Offers a level of flame retardancy for added safety
- **Tensile strength of 8 kg:** Ensures a strong hold for secure bundling
- **Operating temperature range from -40 °C to 85 °C:** Suitable for use in a wide range of environments
- **Width of 2.5 mm:** Allows for easy handling and installation
- **Maximum bundle diameter of 22 mm:** Accommodates various cable sizes

RS PRO Black Standard Cable Tie, 100 mm Length

RS Stock No: 642-836



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a reliable solution for securing cables and wires with its Black Standard Cable Tie. Designed for versatility and durability, this cable tie is ideal for bundling applications in various environments. Its robust construction ensures a secure hold, making it a dependable choice for both industrial and domestic use.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Standard
Tensile Strength	8 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	100 mm
Material	Polyamide
Maximum Bundle Diameter	22 mm
Width	2.5 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

Approvals

Standards/Approvals	ISO 9001 SGS, REACH, RoHS, UL94V-2
---------------------	------------------------------------