



Part Number : [512160700](#)
Product Description : 2.00mm Pitch MicroTPA
Receptacle Housing, Positive Lock, 7 Circuits,
Natural
Series Number : 51216
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings
[512160700_sd.pdf](#)

3D Models and Design Files
[512160700_stp.zip](#)

Specifications
[SPK-51216-001-001.pdf](#)
[PS-51216-006-001.pdf](#)
[PS-51216-007-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	51216
Description	2.00mm Pitch MicroTPA Receptacle Housing, Positive Lock, 7 Circuits, Natural
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Name	MicroTPA
UPC	800754824392

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	7
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	345.700/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No

Temperature Range - Operating	-40° to +105°C
-------------------------------	----------------

Mates With / Use With

Mates with Part(s)

Description	Part Number
MicroTPA Plug Housings	<u>51227</u>
MicroTPA Vertical High Wall Type Headers	<u>55487</u>
MicroTPA Vertical Kinked PC Tail Headers	<u>55755</u>

Use with Part(s)

Description	Part Number
2.00mm Pitch MicroTPA Terminal Position Assurance (TPA) Retainer, 7 Circuits	<u>512170705</u>
2.00mm Pitch Female Terminals	<u>59370</u>
