

Model No. 418

Steel Heavy Duty Lockout Hasp, 1in (25mm) Jaw Clearance

Best Used For:

LOCKOUT/ TAGOUT Lockout Tagout

LOCKOUT/ TAGOUT Safety Lockout/Tagout

Overview & Features

Product Features

- Heavy Duty Pry Proof Lockout Hasp
- Lockout by multiple workers at each lockout point
- Keeps equipment inoperative while repairs or adjustments are being made
- Control cannot be turned on until last worker"s safety padlock is removed from hasp
- Heavy duty pry proof steel
- Dimensions are 2-3/8in x 3-1/4 (60mm x 82mm) with 1in (25mm) inside jaw diameter, holds up to 4 safety padlocks

Product Details

The Master Lock No. 418 Heavy Duty, Pry-proof Steel Safety Lockout Hasp features a 1in (25mm) inside jaw diameter and can hold up to four padlocks. Ideal for lockout by multiple workers at each lockout point, the hasp keeps equipment inoperative while repairs or adjustments are made. Control cannot be turned on until last worker’s padlock is removed from hasp.

Product Specifications

Product Number	418
Lockout Hasp Length	82 mm
Accepts Shackle Diameter up to	7 mm
Colour	Silver
Description	Commercial Bagged
Shelf Pack Qty	12
Master Carton Qty	72

Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu