

Datasheet

RS Pro HSS M4 65 mm Counterbore Drill Bit, 8mm Cutter Diameter, 6 mm Screwed Shank

RS Stock No: **522-7424**



Product Details

RS Pro counterbore drill bit has HSS construction with M4 thread size. This 65 mm long drill bit has a cutter diameter of 8 mm and screwed shank diameter of 6 mm. The right hand cutting counterbore is designed to produce recessed holes for cap headed screws.

Features and Benefits

- 12.5 mm cutter length
- 5.5 mm pilot length
- Pilot diameter of 4.3 mm
- Threaded shank
- 65 mm overall length
- Made from HSS



Specifications:

Cutter Diameter	8 mm
Cutter Length	12.5 mm
Material	HSS
Overall Length	65 mm
Pilot Diameter	4.3 mm
Pilot Length	5.5 mm
Shank Diameter	6 mm
Shank Type	Screwed
Thread Size	M4
Number of Flutes	2