



Datasheet | Balanced Audio Cable

XLR 3-Pin Male | XLR 3-Pin Female | Nickel Plated | 5.00 m | Round | PVC | Dark Grey | Carton Sleeve

Brand: Nedis | Article number: COTH15010GY50 | Product EAN number: 5412810295647

Product specifications

Audio type	Stereo
AWG value	20
Cable design	Round
Cable length	5.00 m
Cable mantle material	PVC
Cable mantle size	6.5 mm
Cable type	XLR
Colour	Dark Grey
Conductor diameter	40 x 0.12 mm
Conductor material	Copper
Connector A	XLR 3-Pin Male
Connector B	XLR 3-Pin Female
Connector design - side A	Straight
Connector design - side B	Straight
Connector material	Metal
Connector plating	Nickel Plated
Material	PVC
Number of products in package	1 pcs
Packaging	Carton Sleeve
SmartLife	No

Packaging information

Brand	Nedis
Order code	COTH15010GY50
EAN single product:	5412810295647
EAN Inner carton:	5412810387397
EAN Outer carton:	5412810353071
Packaging	Header Card
Package contents	1x Balanced XLR Audio Cable

Quantity	L x	W x	H (mm)	Weight
1	30 mm	255 mm	120 mm	261 g
24	300 mm	195 mm	480 mm	6610 g
48	325 mm	420 mm	495 mm	14200 g

