

# Eaton SC20H

Catalog Number: SC20H

Fuse accessory, Fuse-holder, low voltage, 20 A, AC 550 V, BS88/E1, 1P, BS, front connected, black, fuse-link SSD, BS88-2, Optional accessories copper links, padlockable inserts and adaptor carriers

## General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage British standard fuse holder	SC20H UPC 051712419390
EAN	Product Length/Depth
5027590508537	47 mm
Product Height	Product Width
71 mm	25 mm
Product Weight	Warranty
86.7 g	1 year limited
Compliances	
Contact factory	

## Product specifications

### Construction size

Other

### Color

Black

### Connection

Front Connected

### Connection type

Other

### Features

Halogen free

### Mounting method

Screw-on

### Amperage Rating

20 A

### Voltage rating at AC

550 V a.c.

### Number of Poles

Single-pole

### Fuse type

SSD

### Accessories

SSC-LINK, DIN-20-32

### Type

fuse accessory

### Bus-mounting type

No

### Model

Safeclip

### Application

general industrial applications

## Resources

### Brochures

[eaton-bussmannseries-bs88-fuses-industrial-motor-use-product-aid-pa134006-en-gb.pdf](#)

### Catalogs

[SC20H~Eaton Bussmann series low voltage British standard fuse holder Bussmann series complete full line catalog no. 1007](#)

### Specifications and datasheets

[Eaton Specification Sheet - SC20H](#)

### Technical data sheets

[10024 Red spot fuse holders](#)

[10415 Camaster and Safeloc fuse holders](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)