

## LID AND ACCESSORIES

21-704-xxxx and 21-717-0015

### Product specifications

Material: Conductive polypropylene  
(carbon-loaded)

Colour: Black

ESD Marking: All lids marked with ESD sign

Surface resistance:  $\leq 10^4$  Ohm

Usage temperature: 80°C. Please note that depending of load, deformation can appear from 50°C.

Stackability: All containers may be stacked together in a wide range of configurations.

Standard compliance: IEC 61340-5-1



### Dimensions and Part Numbers

Part Number	Dimensions (mm)	Features
21-704-0005	300 x 200	Lid loose
21-704-0010	400 x 300	
21-704-0015	600 x 400	
21-704-0020	300 x 200	Hinged lid with 2 swing latches
21-704-0025	400 x 300	
21-704-0030	600 x 400	
21-704-0035	300 x 200	Lid with 4 swing latches
21-704-0040	400 x 300	
21-704-0045	600 x 400	
21-704-0055	-	Lid hinges
21-704-0060	-	Swing latches
21-717-0015	86x20	Metal label clip

