

Main

Range	Mureva Styl
Range of product	Mureva
Product or component type	Socket-outlet
Device presentation	Complete product
Outlet poles configuration	2P + E
Outlet standard description	Pin earth
Outlet standard deviation	French
Colour tint	Anthracite
Quantity per set	60 pieces

Complementary

Device mounting	Flush Surface
Socket number	1
Rated current	16 A
[Ue] rated operational voltage	250 V AC
Condition of use	Indoor/outdoor
Material	Brass PP (polypropylene) PC (polycarbonate)
Fixing mode	By screws
Clamping connection capacity	1...2.5 mm² for rigid cable(s) 1...2.5 mm² for stranded cable(s) 1...2.5 mm² for flexible cable(s)
Wire stripping length	13 mm
Height	83 mm
Width	83 mm
Depth	46 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Outlet standard	CEE 7/5
[Ue] rated operational voltage	250 V
Connections - terminals	Screwless terminals

Environment

Quality labels	NF
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes