



TOLERANCES: +/- 0.30 mm (+/- 0.012in)

繪圖	DRA'D BY	日期	DATE	材質	MATE.	圖名TITLE:	圖號DWG NO:	版次REVISID:
	JACKY		2010/1/20	ALUMINIUM ALLOY	ADC-12	HQ033		A

ITEM NO	DESCRIPTION
HQ033	NATURAL ALUMINIUM BOX(WITOUT THE GASKET)
HQ033S	@@ IP67 RATING @@(WITH THE SILICON GASKET)
HQ033EMS	@@ IP67 RATING @@(WITH THE SILICON & SHIELDED GASKET)

MATERIAL: ALUMINUM ALLOY #ADC-12

FINISH: NATURAL (NO SUFFIX)  
GRAY (SUFFIX -LG)  
BLACK (SUFFIX -BK)

- 1) EIGHT(8) M4 x 20mm (0.787") LG. SCREWS  
SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE ±0.10mm TOLERANCE  
ALL OTHER DIMENSIONS HAVE ±0.30 mm TOLERANCE



繪圖	DRA'D BY	日期	DATE	材質	MATE.	圖名TITLE:	圖號DWG NO:	版次REVISID:
	JACKY		2010/1/20		ALUMINIUM ALLOY ADC-12	HQ033		A