1626 : Groover GR2-12













The + product :

Grooving up to 12", with accurate depth setting.
Hydraulic jack for fast grooving.
Powerful and silent motor on sturdy frame.

Description

Electrohydraulic groover, produces grooves by cold knurling on standard steel and thin wall pipes Ø 2" – 12". For installing piping, spraying systems, large-size heating and industrial installations.
Compact and highly stable designed for work on worksites and in workshops.
Powerful motor 240 V, 50 / 60 Hz, 1500 W, 23 rpm.
Frame mounted **on 4 feet** for safe man-height work.
Sturdy hydraulic pump with ergonomic control grip; max. pressure: 8,000 kg.
Pressure valve for fast pipe change.
Lower roller storage compartment.

Grooving rollers designed and tempered specifically for minimum wear, with anti-skid surface for more effective tube feed.
Accurate groove depth adjustment with a nut / locknut system, ideal for repetitive work.

Safety pedal for operation control and instant stopping of machine rotation.
Stabilizer for large diameters to prevent tube slipping.
Roller holder for tubes up to Ø 12", fitted with 4 knobs; 2 tempered steel side guides with fast locking system.

Weight (machine only): 129 kg.
Machine dimensions on feet: 770 x 550 x 1400 mm.

More Information

Capacity	For steel or stainless steel pipes Ø 2" – 12" (60 – 325 mm). Pipe wall thickness: 3.5 – 10 mm (steel) / 1.6 – 6.5 mm (stainless steel).
Tips	When grooving stainless steel pipes, use the optional specific lower rollers.
Supplied with	- 4 frame feet. - Safety pedal. - Large diameter stabilizer. - Roller holder. (162615) - Grooving control tape measure. - 3 lower rollers for steel pipe (2" – 2.1/2" ; 3" – 6" ; 8" – 12"). - 2 upper rollers for steel and stainless steel pipe (2" – 6" ; 8" – 12"). - Installation tool set.

References

Sku	Description	Capacity "	kg
162600	Groover GR2-12	2 - 12	170,000
162610	Upper roller 2"-6" for steel / stainless steel pipe	2 - 6	0,780
162611	Upper roller 8"-12" for steel / stainless steel pipe	8 - 12	0,810
162612	Lower roller 2"-2.1/2" for steel pipe	2 - 2.1/2	0,550
162613	Lower roller 3"-6" for steel pipe	3 - 6	1,250
162614	Lower roller 8"-12" for steel pipe	8 - 12	1,420
162616	Lower roller 2"-2.1/2" for stainless steel pipe	2 - 2.1/2	0,550
162617	Lower roller 3"-6" for stainless steel pipe	3 - 6	1,250
162618	Lower roller 8"-12" for stainless steel pipe	8 - 12	1,420
162615	Pipe holder for grooving machine	2 - 12	29,000

