

Product Datasheet

4 piece SMT tweezer set 120mm

RS- 8211508



Standard features:

- Special mechanical devices tweezers with 4 different in one fusion model.
- Resistor and capacitor repair tooling
- 4 lbs spring tension of tweezers is best for normal workmanship.
- Material is medical grade stainless steel which is completely the best grade for instruments.

Technical data

- Dimensions: 120X9X7mm (length x breath x height) excluding packing three models and one
- Tips are different for all four models
- Tips of model one is 45degree curved with 1mm diameter hole in tips to hold cylindrical 1mm resistors, capacitors or any other products in line for repair with same diameter.
- Tips of 2nd model is finest with 45degree angular
- Tips of 3rd model is 7 shaped to hold deep hole products with finest in tips.
- Tips of 4th model is spade model with tips curved for 2.5mm capacitor holder rounds in it can be used for almost 2mm to 3.5mm cylindrical items holder.
- Stainless steel brushed finish.
- Weight : 90 grams

Package includes:

- Packed single unit in PVC pouch clear.