

Professionally approved products.

Datasheet

I.E.E. Strain Gauge

RS Stock number [189-5562](#)



Specifications:

- Gauge Resistance: $>1\text{M}\Omega$
- Length: 48.8mm
- Maximum Current: 1mA
- Maximum Operating Temperature: $+170^{\circ}\text{C}$
- Minimum Operating Temperature: -30°C
- Width: 11.7mm