

neofeu.com


## STOPEDGE GUIDED TYPE FALL ARRESTER ON FLEXIBLE ANCHORAGE LINE

REF.

NSL17AD.10 .20 .30

FALL PROTECTION ONLY\*

CERTIFICATION: EN 353-2:2002 / REGULATION: 2016 / 425 SHEETS: VG11.062 / VG11.075



## TECHNICAL SPECIFICATIONS

- Vertical and horizontal use
- Maxi user weight 140 kg
- Polyamide kernmantel rope Ø12mm (Static resistance > 22 kN)
- Tribofinishing steel sliding fall arrester
- Static resistance on rope >15 kN
- Braking force < 6 kN
- Zinc plated steel screw gate connector opening 18 mm for connexion of the line to the anchor point
- Zinc plated steel automatic locking connector opening 18mm for connexion to the full body harness
- Weight: 2,0 kg (NSL17AD.10)

Length of flexible anchorage line: 10, 20 and 30 meters.

## **DESCRIPTION**

Non opening fall arrester sliding up and down on a kernmantel rope (flexible anchor line).

Compatible in a horizontal use for a maximum load up to 140kg. Fitted with a polyamide webbing shock absorber, a NM16NS screw gate connector to the anchor line to fix to the structure and an automatic hook to connect to the attachment point on the harness.

## **USE**

Works on height on roofs with vertical fall hazards. Adapted for the industry, the construction and telecom industry.