Product data sheet Characteristics

ZB4FA5

Flush mounted push button head, Harmony XB4, metal, yellow, 30mm, spring return, unmarked





Main

Range of product	Harmony XB4	
Product or component type	Head for non-illuminated push-button	
Device short name	ZB4F	
Bezel material	Chromium plated metal	
Mounting diameter	30.5 Mm	
Sale per indivisible quantity	1	
Head type	Built-in-flush	
Shape of signaling unit head	Round	
Type of operator	Spring return	
Operator profile	Yellow flush, unmarked	

Complementary

Device presentation	Basic element
	C15 for <1 contacts using single blocks in front mounting
	C11 for <3 contacts using single blocks in front mounting
	C2 for <9 contacts using single and double blocks in front mounting
Electrical composition code	C1 for <9 contacts using single blocks in front mounting
Mechanical durability	10000000 Cycles
CAD overall depth	31 Mm
CAD overall height	36.6 Mm
CAD overall width	36.6 Mm

Environment

Protective treatment	TH	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-4070 °C	
Overvoltage category	Class I conforming to IEC 60536	
IP degree of protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529 IP69 conforming to IEC 60529 IP69K conforming to ISO 20653 Type 13 conforming to UL 50E Type 12 conforming to UL 50E Type 4 conforming to UL 50E Type 4X conforming to UL 50E	
IK degree of protection	IK06 conforming to IEC 50102	

Standards	CSA C22.2 No 14
	EN/IEC 60947-5-1
	EN/IEC 60947-5-4
	UL 508
	EN/IEC 60947-1
	JIS C8201-5-1
	CE
	JIS C8201-1
Product certifications	UL listed
	CSA
	CCC
	EAC
Vibration resistance	5 gn (f= 10500 Hz) conforming to IEC 60068-2-6
	25 mm peak to peak (f= 210 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming-
	to IEC 60068-2-27
	50 gn (duration = 11 ms) for half sine wave acceleration conforming-
	to IEC 60068-2-27
	25 gn (duration = 6 ms) for 1000 shocks on each axis conforming-
	to IEC 60068-2-27

Packing Units

1 doking office	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.3 Cm
Package 1 Width	5.2 Cm
Package 1 Length	5.5 Cm
Package 1 Weight	58.0 G
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	4.3 Cm
Package 2 Width	5.5 Cm
Package 2 Length	26.5 Cm
Package 2 Weight	297.0 G
Unit Type of Package 3	S02
Number of Units in Package 3	80
Package 3 Height	15.0 Cm
Package 3 Width	30.0 Cm
Package 3 Length	40.0 Cm
Package 3 Weight	5.06 Kg

Offer Sustainability

Green Premium product REACh Declaration Yes
Yes
Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Yes
Yes
☐ China RoHS Declaration
₫Yes
Product Environmental Profile
End Of Life Information
WARNING: This product can expose you to chemicals including: Di-isode-cyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov



Contractual warranty

Warranty 18 months

Product Life Status : Commercialised