



Pushing Performance
Since 1945

VB RJ45 LaR -DB RJ45 FRNC grey 7.5m




Image is for illustration purposes only. Please refer to product description.

Part number	09 48 858 7585 075
Specification	VB RJ45 LaR -DB RJ45 FRNC grey 7.5m
HARTING eCatalogue	https://harting.com/09488587585075

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING VarioBoot RJ45 Preferred directions left/right
Connector 2	HARTING DualBoot RJ45
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Flame retardant Halogen-free

Version

Cable length	7.5 m
Number of cores	8
Core structure	4x 2x AWG 26/7

Technical characteristics

Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-20 ... +60 °C unmoved 0 ... +60 °C moved
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (cable)	FRNC (LSZH)
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	ISO/IEC 11801 IEC 61156-6 IEC 60332-1 Flame retardancy IEC 60754-2 Halogen freeness IEC 60754-2 Non corrosive IEC 61034 Low smoke
----------------	--

Commercial data

Packaging size	1
Net weight	305 g
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140269675
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600