

Technical data sheet

Article number:
924-00456

BSW5

Product Group	Heat Shrink Crimp Link (Waterproof Connectors)
Product Family	Single Grip Pre-Insulated Terminals
Material	Copper (CU), Polyvinylchloride (PVC)
Colour	Yellow (YE)

Application Range	Low Voltage
Conductor Size Range mm²	4.0-6.0 mm ²
Diameter (D)	7.4 mm
Halogen-free	Yes
Length (L)	40.5 mm
Length (L2)	15 mm
Max Current	48 A
Max Voltage	600 V
Operating Temperature	+75 °C
Package Content	50 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
Ø (D2)	4.05 mm
ROHS compliant	Yes

HF ✓

RoHS ✓