

DELTA profil, titanium white SCHUKO socket outlet 10/16 A 250 V
 With screwless Connection terminals Cover plate 65x 65 mm without
 claws



Model	
Product brand name	DELTA
Product designation	SCHUKO socket outlet
Cover version	central plate
Design of the special power supply unit	without special current supply
Design of the socket / according to VDE 0620 for severe conditions	No
Design of the phase tap	No
General technical data	
Marking / of socket outlet	without imprint
Mounting type	fixing with screw
Surface processing	others
Material	thermoplastic
Supply voltage	
Operating voltage / Rated value	250 V
Protection class	
Protection class IP	IP20
Main circuit	

Operating current	
• Rated value	16 A

Appearance

Color	white
-------	-------

Product details

Product component	
• Ejection equipment	No
• Labeling field	No
• Increased touch protection	No
• Fault current protection	No
• miniature fuse	No
• Integrated / functional lighting	No
• Integrated / Light source	No
• Integrated / orientation lighting	No
• Hinged lid	No
Product feature	
• lockable	No
• halogen-free	Yes
• transparent	No

Product function

Product function	
• Socket selectable	No
• Overvoltage protection	No

Number

Number of units	1
Number of sockets / switchable	0

Connections

Arrangement of contacts / diagonal	No
Type of electrical connection	plug terminal

Mechanical Design

Height	70 mm
Width	70 mm
Depth	45 mm
Mounting type	flush mounted
Material / of the enclosure	plastic

Certificates



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5UB1403-0KK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5UB1403-0KK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5UB1403-0KK

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

