



PRODUCT-DETAILS

TY100-18-39-100

TYFAST 2,4X111MM NATURAL HEAT STAB.



General Information

Extended Product Type	TY100-18-39-100
Product ID	7TCG054360R0084
EAN	5414363060291
Catalog Description	TYFAST 2,4X111MM NATURAL HEAT STAB.
Long Description	Cable Tie, Heat Stabilized Natural Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 102.1mm (4.02 Inches), Width of 2.54mm (0.10 Inches), Thickness of 1.12mm (0.04 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), 100 Pack

Ordering

EAN	5414363060291
UPC	786210840505

Dimensions

Product Net Width	0.1 in 2.54 mm
Product Net Depth / Length	4.02 in 102.1 mm

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	5 in 127 mm
Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	7 in 178 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	11.4 in 290 mm
Package Level 2 Height	9.1 in 231 mm
Package Level 2 Depth / Length	15 in 381 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	1 in 25.4 mm
Color	Natural
Effective Date	20020508
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	OTHER ARTICLES OF PLASTICS
Product Type	Heat Stabilized
Standards	UL E49405
Tensile Strength	18 lb 80 N
Thickness	0.04 in 1.12 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY100-18-39-100
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY100-18-39-100

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

