


Technical data sheet

Article number:
111-95208

MBT20XHS



Product Group	Cable ties with ball-lock
Product Family	MBT-Series, stainless steel 304
Material	Stainless Steel (SS304)
Colour	Metal (ML)
Application Tool	KST-STG200, HDT16, MK9SST, MK9PSST
Bundle Ø max.	152.0 mm
Bundle Ø min.	17.0 mm
Flammability	non-burning
Halogen-free	Yes
Length (L)	521.0 mm
Min.Tensile Strength	2700 N
Operating Temperature	-80 °C to +538 °C
Package Content	50 pcs.
Package Content packed in	pack
Releasable Closure (Yes/No)	No
Thickness (T)	0.3 mm
UV-Stabilised	Yes
Variant	Not Serrated
Weight/Unit	0.0178 kg
Width (W)	12.3 mm

HF ✓ LFH ✓ RoHS ✓