



# Sounds like productivity



Includes 2-port charging dock

## RX680

PMR446 Two-Way Radios



### Rugged & splashproof

IP54 certified protection with up to 10 km range and LCD display



### Ultra-long runtime

Stay connected all day with up to 18 hours of battery life



### 16 Channels

Securely communicate across 16 channels with 121 privacy codes



### Patented VibrAlert®

Feel incoming alerts ensuring you never miss a transmission



### Built-in flashlight

Illuminate dark areas or signal for help with a single button



### Voice-activated transmission (VOX)

Hands-free usage to automatically transmit when you speak

### EMERGENCY ALERT

Dedicated button for time-sensitive or emergency situations

### ERGONOMIC CONTROLS

Large, tactile dedicated volume knob for one-handed operation

### 2.5 MM JACK HEADSET JACK

Choose from a range of headset accessories, including speaker mic and headset functionality

### USB-C JACK

For charging without a dock



### DOCK CHARGER

Includes 2-port charging dock



### CHARGING CABLE

USB-C cable



### BELT CLIP

Keep your radio secure and within reach with this simple, durable belt clip

### LITHIUM-ION BATTERY

Up to 18 hours of battery life keeps you connected for your entire workday

| Part#     | Two-Way Radio Description                     | QTY  |
|-----------|-----------------------------------------------|------|
| 0190001-1 | PMR446 two-way radio, includes 2-dock charger | 2 pk |

| Part#      | Accessory Headsets Description             | QTY  |
|------------|--------------------------------------------|------|
| GA-SV01    | Surveillance style headset with microphone | 1    |
| GA-SV01 2P | Surveillance style headset with microphone | 2 pk |
| 0010120-1  | D-Style headset                            | 1    |
| 0010121-1  | C-Style around the ear headset             | 1    |
| 0010122-1  | C-Style In ear headset                     | 1    |
| 0010123-1  | C-Style in ear headset with foam earpiece  | 1    |