



Datasheet

ENGLISH



RS 811-7080

Specifications

Aggregate Locally Power Metered 1U Horizontal PDU with:-

- 6 x UK BS1363 Sockets
- Local Power Meter Display (Scrolls through Amps, Volts, Watts and Power Factor)
- 3 Metre Back Fed Lead
- 230V/32A Single Phase IEC60309 Plug
- Black Finish

Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	230V
Amperage	32A
VA per Input (Load Capacity)	7.3kW
Frequency	50/60 Hz
Over Current Protection	None
Switch	None
Power Cable Wire Gauge	4mm ² H07RN-F
Power Cable Length	3m
Plug Type	IEC60309 2P + E, 32A, 250V
Receptacle/Socket Type #1	UK BS1363
Quantity on Face #1	6
Style #1	Individual
Maximum Output per Receptacle/Socket #1	13A per receptacle bank
Voltage per Receptacle/Socket #1	230V
Heavy Steel -Black Powder Coat	Yes
Configuration	1U Horizontal
Product Warranty	Three Year
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 60950, EN 55022 and EN 55024
Chassis Dimensions (LxWxD)	483mm x 50mm x 44mm