

Pliers set Industrial electric Combination pliers, needle nose pliers, diagonal cutters 3-pcs. (38637)



Wiha Werkzeuge GmbH
Obertalstraße 3-7 78136 Schonach
E-Mail: info.de@wiha.com
Tel.: +49 (0)7722 959-0



Order no.: 38637

Article number: Z99000109

EAN: 4010995386375

Customs tariff number: 82032000

Increases your efficiency: Wiha needle nose pliers with extra-long plier head for inserting low-lying components.

Protects your health: Special DynamicJoint® design reduces effort required for cutting.

Offers you full protection: Each tool individually tested at 10,000 V AC and approved for 1,000 V AC.

Increases your safety: Wiha combination pliers enable safe, non-slip gripping in all work situations.

Application: For work in the area of live parts up to 1,000 V AC.

Application: All tools suitable for use with or near live components up to 1,000 V AC.

Manufactured acc. to IEC 60900.

Content:

- 1x Industrial electric diagonal cutters with DynamicJoint® 160 mm, 6 1/2" (43336)
- 1x High-leverage industrial electric combination pliers with DynamicJoint® and OptiGrip with extra long cutting edge 180 mm, 7" (33186)
- 1x Industrial electric needle nose pliers with cutting edge straight shape 200 mm, 8" (33178)

Customs tariff number	82032000
-----------------------	----------

Blister packed	No
----------------	----

VDE article	Yes
-------------	-----

Country of origin (ISO 3166-1 Alpha 3)	VNM
-------------------------------------------	-----
