



changeover operating mechanism for 3RT105.-X..-0LA2 or 3RT145.-X..-0LA2 110 V DC x (0.7-1.25) supply voltage PLC input 24...110 V DC spring-loaded terminal

|                                |                                                                                                                                                                                                           |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| product category               | Solenoid coils                                                                                                                                                                                            |
| product designation            | Changeover operating mechanism                                                                                                                                                                            |
| product type designation       | 3RT19                                                                                                                                                                                                     |
| General technical data         |                                                                                                                                                                                                           |
| Substance Prohibittance (Date) | 09/06/2016                                                                                                                                                                                                |
| SVHC substance name            | Lead - 7439-92-1<br>Lead monoxide (lead oxide) - 1317-36-8<br>2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol - 79-94-7<br>Perfluorobutane sulfonic acid (PFBS) and its salts - -<br>Melamine - 108-78-1 |
| Weight                         | 0.538 kg                                                                                                                                                                                                  |

|                          |     |                   |
|--------------------------|-----|-------------------|
| Approvals Certificates   |     |                   |
| General Product Approval | EMV | Test Certificates |



EG-Konf.



UL



RCM

[Special Test Certificate](#)

|                   |                      |       |
|-------------------|----------------------|-------|
| Test Certificates | Maritime application | other |
|-------------------|----------------------|-------|

[Type Test Certificates/Test Report](#)



ABS



DNV



PRS



RMRS



|       |         |             |
|-------|---------|-------------|
| other | Railway | Environment |
|-------|---------|-------------|

[Confirmation](#)


[Miscellaneous](#)

[Special Test Certificate](#)

[Environmental Confirmations](#)

## Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>  
Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>  
Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT1955-5XF42>  
Cax online generator



last modified:

10/11/2025