

RS Part Number: **795-2204**

Specifications and dimensions



- Boxed Isolator 32 A DC 4 Pole
- 1000 V Rating for PV Applications
- Positive Snap Action Self Cleaning Contacts

Features	
Height	170 mm
Width	102 mm
Depth	80 mm
Depth including switch	110 mm
Degree of protection	IP65
Standard	IEC 60364-7-712
Maximum cable capacity	16 mm ²
2 poles connected in series:	
Maximum switching current DC21 600V	32 A
Maximum switching current DC21 800V	23 A
Maximum switching current DC21 1000V	13 A
2 poles in parallel connected in series to 2 poles in parallel:	
Maximum switching current DC21 600V	32 A
Maximum switching current DC21 800V	23 A
Maximum switching current DC21 1000V	13 A
4 poles connected in series:	
Maximum switching current DC21 600V	32 A
Maximum switching current DC21 800V	32 A
Maximum switching current DC21 1000V	32 A