

PX0409/90 Datasheet

 [View Product Page](#)

Product Name // 90 Degree SMB Antenna 850-900Mhz/1800Mhz/1900MHz



// Product Description:

- SMB Antennas
 - Water and dustproof to IP68 when mated with compatible connector
 - Secure screw thread locking
 - Built-in half wavelength omnidirectional sealed antenna
 - Choice of two presentations depending on part code:
 - 90 degree bend (part codes suffixed /90)
 - Straight (no part code suffix)
- SMB 50 Ohm interface
 - Choice of frequency bands depending on part code:
 - PX0407, PX407/90 - 2.4Ghz-2.5GHz
 - PX0408, PX408/90 - 440MHz-470MHz
 - PX0409, PX409/90 - 850-900Mhz/1800Mhz/1900MHz
 - Mate with PX0414 Panel Mount SMB Connector

// General Information:

Product Display Title:	SMB Antennas
Product Family:	Circular Data Connectors
Product Series:	400 Series - Wireless Buccaneer
Body Material:	PVC
Body Material Type:	Plastic Body
Contact Type:	Plug Contact
Coupling Type:	Screw
Diameter Over Coupling Ring Mm:	19.1mm
Flamability Rating:	UL94V-0
Function:	Antenna
Ip Rating:	IP68, IP69K
Max Operating Temperature:	+80°C
Min Operating Temperature:	-40°C
Number Of Contacts:	1 Contact

// Product PDF Links



// Product 3D CAD Model Links



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)