



 PRODUCT-DETAILS

AT28/M25/A/BLY

STR PA66 FITTING M25 28MM-BLY



General Information

Extended Product Type	AT28/M25/A/BLY
Product ID	7TCA296170R0396
EAN	5020963037535
Catalog Description	STR PA66 FITTING M25 28MM-BLY
Long Description	Adaptalok ATS, Straight Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 28mm, M25 Thread, Polyamide (Nylon) 66/TPE, Black with Yellow Elastomer

Additional Information

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

Ordering

EAN	5020963037535
UPC	786210282688

Technical

Number of Batteries	0
Color	Black/Yellow Elastomer
Material	Polyamide/Nylon 6.6
Size	NC 28mm

Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963037535
Package Level 1 Height	11.81 in 300 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
ETIM 9	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

